


GRINDERS

SANI-GRINDER

The Sani-Grinder is built for shaping, grinding and polishing orthotic appliances. Low speed allows for shaping and reduction of plastics, foams and leather, while the high speed provides polishing and faster reduction of orthotic appliances, podiatric and other materials.

Ref.: ALI-7628 110V, 60Hz
Ref.: ALI-7628-220 220V, 50Hz

The integral rear suction filter bag is easily removed and emptied with the aid of an encased zipper.




Rear View

DOUBLE SIDED SANI-GRINDER

The double sided Sani-Grinder is designed with two 3"x3" sanding sleeves - one each mounted on the left and right side of the unit. Built for the laboratory which produces custom orthotic appliances, it is fitted with a coarse and fine 3"x3" abrasive wheel for fast or slower reduction of various materials. Two speeds allow for easy shaping and polishing of ortho application.

Ref.: ALI-7627 110V, 60Hz



STAND UP SANI-GRINDER/POLISHER

An industrial Sani-Grinder/Polishing unit built for the large orthotic laboratory which creates various podiatric and orthotic appliances on a daily basis. This unit is powered by a 3/4 HP industrial duty suction motor which produces 600 CFM (cubic feet per minute) suction power to collect dusts, debris and polishing compounds.

24 shakable cloth filter bags entrap 0.5 micron particles. Collected dusts are shaken from the filter bags and deposited into a lower internal, removable dust tray with the aid of an external foot shaking pedal. A double sided ALI-7627 is mounted on a melamine covered table top.

Ref.: ALI-70075 110V, 60Hz




Built to provide years of durable service.

GRINDER ACCESSORIES

REPLACEMENT RUBBER SANDING DRUM

Complete for 3"x3" Sanding Sleeves.

Ref.: ALI-7001



TAPERED CHUCK


Used to accommodate buffing wheels and brushes. Placed directly onto the shaft of the Sani-Grinder after removal of the sanding drum.

Ref.: ALI-7003



SANDING SLEEVES

Size: 3"X3".




Ref	Description
ALI-76281C	Coarse Grit, 40
ALI-76282M	Medium Grit, 60
ALI-76283F	Fine Grit, 100

STONE CHUCK

Used to mount a large grinding wheel onto the shaft of the Sani-Grinder after removing the Sanding Drum for the shaft.


Ref.: ALI-7002



JACOB'S TYPE CHUCK

Used for gross work. Accommodates 0-1/4" diameter burs and drills used to create podiatric and orthotic appliances.

Ref.: ALI-7004



SANDING SLEEVES FOR PNEUMATIC DRUMS

Ref	Diameter	Width	Grit
AC-T80931	3"	6"	36
AC-T80947	3	6"	36
AC-T80935	3.5"	7"	80
AC-T80951	3.5"	7"	80



SANDING SLEEVES FOR PNEUMATIC DRUMS

Ref	Diameter	Width	Grit
AC-T80955	6"	7"	40
AC-T80956	6"	7"	60
AC-T80957	6"	7"	80

